O MBE Komponenten | dr. eberl

VALVED SULFUR CRACKER SOURCE VCS

- Provides cracked or uncracked sulfur flux
- Flux modulation and on/off control by motorized valve
- Source capacity 300 and 500 cm³
- Water-cooled assembly
- Excellent flux uniformity due to beam shaping nozzle
- Precise run-to-run reproducibility



Production scale valved sulfur source VSS-9600

The VCS is a valved sulfur cracker, employed in high efficiency CIS solar cell growth and other II-VI semiconductor material deposition applications.

Sulfur beam pressure is generated in a heated large capacity crucible. The sulfur flow rate is controlled and switched on/off by a specially designed sulfur-resistant valve whose outlet opens into an injection tube that includes an independently heated cracking zone. The temperature within the cracking zone can be adjusted to generate either uncracked or cracked sulfur. The use of a beam shaping nozzle at the end of the injection tube provides excellent flux uniformity on the substrate.



Valved Sulfur Cracker Source VCS-300 with 300 $\rm cm^3$ crucible and DN63CF (0.D. 4.5") mounting flange

The valve design features a large cross-section orifice which allows very good pumping properties of the reservoir. Its robust wide angle valve design effectively eliminates the risk of locking, which is a frequently observed problem with needle valves.

Technical details of the construction have been optimized to meet the specific requirements of research deposition applications and MBE systems. Simple system integration and excellent long-term run-to-run stability have been demonstrated. Different crucible sizes of 300 cm³ or 500 cm³ are offered on DN63CF (0.D. 4.5").

The figure on the left side shows an industrial version, applied in sulfurization processes that are part of solar cell manufacturing and other industrial thin film applications.

Applications

The VCS Valved Sulfur Cracker Source has been designed for the controlled evaporation of sulfur. It can used for II-VI semiconductor thin film research and solar cell manufacturing. Other possible applications are, for example, post-growth sulfurization processes.MBE-Komponenten provides support in the design of customerspecific research or production systems in order to achieve a customized source geometry, optimized for specified layer uniformity and most efficient deposition material consumption. Co-deposition processes can be simulated on request. The simulations are based on geometric and Monte Carlo method calculations. Typical results include the lateral layer thickness distribution and material composition for multiple material codeposition processes on semiconductor wafers as well as on large area substrates. Please contact us for more information.

O MBE Komponenten | dr. eberl

Technical Data		
Туре	VCS-300	VCS-500
Crucible capacity	300 cm ³	500 cm ³
Mounting flange	DN63CF (0.D. 4.5")	DN63CF (O.D. 4.5")
Length of injector tube	250 to 400 mm	250 to 400 mm
In-vacuum diameter	38 mm	38 mm
(w/o cooling shroud)		
External dimensions	see drawing below	contact us
Operating temperatures		
-crucible zone	150 - 300°C	150 - 300°C
-cracker (no cracking)	400°C	400°C
-cracker (cracking)	800 - 1000°C	800 - 1000°C
Max. bakeout temperature	300 / 1200°C	300 / 1200°C
(crucible/cracker)		
water cooling	main body	main body
	injector tube (option)	injector tube (option)
Valve opening time	1 sec	1 sec
Heater circuits	crucible + valve	crucible + valve
	cracker	cracker
Thermocouples	W5%Re/W26%Re	W5%Re/W26%Re
	2 thermocouples	2 thermocouples
	crucible-valve / cracker	crucible-valve / cracker
Valve control	manual or motor drive	manual or motor drive
	MVCU	MVCU

Details to larger versions on request



Schematic drawing of the Valved Sulfur Cracker Source VCS (Drawing shows VCS-300)

Dr. Eberl MBE-Komponenten GmbH Josef-Beyerle-Str. 18/1 71263 Weil der Stadt, Germany Fon+49 7033 6937-0Mailinfo@mbe-components.comWebwww.mbe-components.com